

IP hood for lens

P/N: T300075ACC

Copyright

© 2022, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T300075ACC

Commit: 79359

Language:

Modified: 2021-09-14

Formatted: 2022-02-03

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description	
The IP hood makes the FLIR A400/A500/A700 and FLIR GF77a cameras safe to use in IP66 environments.	
NOTE:	
<ul style="list-style-type: none"> When the IP hood is mounted on the camera, it blocks the LED torch on the front of the camera, which means that the torch cannot be used. To fulfill the accuracy specification, the camera should not be exposed to temperature changes of more than 0.5 °C/min. 	
Shipping information	
Packaging, type	Cardboard box
List of contents	<ul style="list-style-type: none"> IP hood O-ring Screws (3 pcs.) Printed documentation
Packaging, size	151 × 125 × 125 mm (5.94 × 4.92 × 4.92 in)
EAN-13	7332558025864
UPC-12	845188021702

Compatible with the following products:

- 85900-0000; FLIR A700 Thermal Core
- 85901-0101; FLIR A700-EST 24°
- 85902-0101; FLIR A700-EST 42°
- 85902-0102; FLIR A700 24° Professional Science Kit
- 85902-0202; FLIR A700 24° Standard Science Kit
- 85903-0102; FLIR A700 24° f/1.0 Professional Science Kit
- 85903-0202; FLIR A700 24° f/1.0 Standard Science Kit
- 90600-0000; FLIR A500 Thermal Core
- 90601-0101; FLIR A500-EST 24°
- 90602-0101; FLIR A500-EST 42°
- 91900-0000; FLIR A400 Thermal Core
- 91902-0202; FLIR A400 24° Standard Science Kit
- 91903-0102; FLIR A400 24° Professional Science Kit
- 86401-0101; FLIR GF77a 25° LR